

Project:		
Fixture Type:		
Location:		
Contact:		

P350039-020

Briarwood

The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs. A rich Oak and Antique Bronze finish combination. Two-Light flush mount.

- Features a classic pattern commonly found on barn or farmhouse doors and gates
- Faux-painted wood-look enclosure to frame vintage-style light bulbs.
- · Rich, painted oaky finish paired with an Antique Bronze finish.

Category: Close-to-Ceiling Finish: Antique Bronze (painted) Construction: Steel Construction



Square: 12 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush-Mount mounted	Prewired	Quantity: Two 60 W max. Medium Base or	CULus Dry Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base socket	
Fixture covers a standard 4" recessed outlet box: 11.25" W., 1.0625" ht., 11.25" depth			