

TYPE:

DATE:

NAME:

PROJECT:

Incandescent

P3925-09ET Dome Glass CTC

Two-light flush mount with dome shaped etched glass, solid trim and decorative knobs. Center lock-up with matching finial.

- Brushed Nickel finish.
- Etched glass.
- Decorative details.

Category: Close-to-Ceiling Finish: Brushed Nickel (plated) Construction: Steel Construction Glass/Shade: Etched glass bowl



Diameter: 13-1/4" Height: 5-13/16"

Glass Width: 9-13/16" Height: 3-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted	Pre-wired	Quantity:	cCSAus Damp location listed
Mounting strap for outlet box included Ceiling pan covers a standard 4" octagonal recessed outlet box 13.1875" W., 1.375" ht., 13.1875" depth	6" of wire supplied 120 V	Two 75w max. Medium Base E26 base ceramic sockets	1 year warranty