



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3955-09

Heart

Three-light Brushed Nickel inverted pendant with etched glass bowl and curvaceous arms.

Category: Hall & Foyer

Finish: Brushed Nickel (plated)

Construction: Steel construction construction

Glass: Etched glass bowl



Diameter: 17-3/4"

Height: 21-3/4"

Overall ht. w/chain: 65-3/4"

Glass: 17-3/4" dia.

Height: 5-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included 42" 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 5-1/8" dia., 15/16"	Pre-wired 8 feet of wire supplied 120V	Quantity: 3 100W Medium Base Medium porcelain sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Post top lantern, Wall bracket, fixtures are available



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3955-09

Heart

Three-light Brushed Nickel inverted pendant with etched glass bowl and curvaceous arms.

Category: Hall & Foyer

Finish: Brushed Nickel (plated)

Construction: Steel construction construction

Glass: Etched glass bowl



Diameter: 17-3/4"

Height: 21-3/4"

Overall ht. w/chain: 65-3/4"

Glass: 17-3/4" dia.

Height: 5-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included 42" 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 5-1/8" dia., 15/16"	Pre-wired 8 feet of wire supplied 120V	Quantity: 3 100W Medium Base Medium porcelain sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Post top lantern, Wall bracket, fixtures are available