

DATE:

NAME:

PROJECT:

Incandescent

P400047-020

TYPE:

Briarwood

The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs. A rich Oak and Antique Bronze finish combination. Four-Light chandelier.

- Features a classic pattern commonly found on barn or farmhouse doors and gates
- Faux-painted wood-look enclosure to frame vintage-style light bulbs.
- Rich, painted oaky finish paired with an Antique Bronze finish.

Category: Chandeliers

Finish: Antique Bronze (painted) Construction: Steel Construction



Square: 20" Height: 12" Overall Ht. W/Stem: 88"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of	15 feet of wire supplied 120 V	Four 100w max. Medium Base E26 base socket	1 year warranty
Stem included Canopy covers a standard 4" octagonal recessed outlet box 6" W., 1" ht., 6" depth			