

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400198-031 Lassiter

Manifest a swoon-worthy lighting experience with the stunning blend of the modern and traditional styles in this one-of-a-kind chandelier. Square tubing with clean, sharp angles is coated in a beautiful matte black finish that demands your attention. Striking vintage light sockets boast their bold yet simple demeanor as they hold clear glass shades to complete this statement-making light fixture.

- Coated in a matte black finish.
- Square tubing with clean, sharp angles.
- Striking vintage light sockets demand your attention.
- Clear glass shades complete the blend of modern and traditional styles.
- Ideal for any foyer, kitchen, or dining room.
- Measures 32-inch width by 29-inch height.
- Perfect for modern, new traditional, or contemporary settings.
- Uses nine medium base bulbs that are sold separately (60w max - LED or incandescent).
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade



Diameter: 32 in
Height: 29 in
Overall Ht. W/Chain: 152 in

Clear glass Cylindrical Shade
Width: 4 in
Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Nine 60 W max. Medium Base or LED equivalent	CULus Dry Location Listed
1/4 IP mounting plate for outlet box included	15 feet of wire supplied	E26 base Porcelain sockets	1-year Limited Warranty
10 feet of 9 gauge chain supplied	120 V		
Canopy covers a standard 4" recessed outlet box: 5.5" W., 1.125" ht., 5.5" depth			