

ELECTRONIC CABLE PLENUM RATED



PLENUM RATED - MULTI-CONDUCTOR UNSHIELDED										
TWC PART NUMBER	SW PART NUMBER	DESCRIPTION	AWG	# COND	NOM. DIAM. (inch)	PACKAGING			JACKET COLOR	UL/NEC®
						TYPE	LENGTH	lbs/1000 ft		
Burglar alarm, public address systems, intercoms, telephone stations, speakers, instrumentation & control, sunlight resistant. For all power-limited circuits use.										
P20031.1A	57563202	22/2C STR BC N/S WHT	22	2	0.118	REELS	1000'	9	WHITE	CMP/CL3P
P20031.1B	57563201	22/2C STR BC N/S WHT	22	2	0.118	REELEX	1000'	9	WHITE	CMP/CL3P
P20035.1A	57563302	22/4C STR BC N/S WHT	22	4	0.137	REELS	1000'	15	WHITE	CMP/CL3P
P20035.1B	57563301	22/4C STR BC N/S WHT	22	4	0.137	REELEX	1000'	15	WHITE	CMP/CL3P
P20177.1B	57563501	22/4C STR BC N/S WHT	22	4	0.128	REELEX	1000'	14	WHITE	CMP/CL3P
P20008.1A	57563002	22/6C STR BC N/S WHT	22	6	0.155	REELS	1000'	21	WHITE	CMP/CL3P
P20008.1B	57563001	22/6C STR BC N/S WHT	22	6	0.155	REELEX	1000'	21	WHITE	CMP/CL3P
P20008.1D	57563003	22/6C STR BC N/S WHT	22	6	0.155	REELEX	500'	21	WHITE	CMP/CL3P
P20018.1A	57563102	22/8C STR BC N/S WHT	22	8	0.179	REELS	1000'	27	WHITE	CMP/CL3P
P20044.1A	57563402	22/12C STR BC N/S WHT	22	12	0.223	REELS	1000'	39	WHITE	CMP/CL3P
P30016.1A	57569202	20/2C STR BC N/S WHT	20	2	0.13	REELS	1000'	12	WHITE	CMP/CL3P
P30016.1B	57569201	20/2C STR BC N/S WHT	20	2	0.13	REELEX	1000'	12	WHITE	CMP/CL3P
P40020.1A	57563602	18/2C STR BC N/S WHT	18	2	0.154	REELS	1000'	17	WHITE	CMP/CL3P
P40020.1B	57563601	18/2C STR BC N/S WHT	18	2	0.154	REELEX	1000'	17	WHITE	CMP/CL3P
P40020.1C	57563604	18/2C STR BC N/S WHT	18	2	0.154	REELS	500'	17	WHITE	CMP/CL3P
P40024.1A	57563702	18/3C STR BC N/S WHT	18	3	0.165	REELS	1000'	24	WHITE	CMP/CL3P
P40024.1B	57563701	18/3C STR BC N/S WHT	18	3	0.165	REELEX	1000'	24	WHITE	CMP/CL3P
P40031.1A	57564002	18/4C STR BC N/S WHT	18	4	0.184	REELS	1000'	30	WHITE	CMP/CL3P
P40031.1B	57564001	18/4C STR BC N/S WHT	18	4	0.184	REELEX	1000'	30	WHITE	CMP/CL3P
P40065.1A	57564102	18/6C STR BC N/S WHT	18	6	0.218	REELS	1000'	44	WHITE	CMP/CL3P
P40065.1C	57564104	18/6C STR BC N/S WHT	18	6	0.218	REELS	500'	44	WHITE	CMP/CL3P
P40030.1A	57563802	18/8C STR BC N/S WHT	18	8	0.239	REELS	1000'	57	WHITE	CMP/CL3P
P50032.1A	57564202	16/2C STR BC N/S WHT	16	2	0.178	REELS	1000'	25	WHITE	CMP/CL3P
P50032.1B	57564201	16/2C STR BC N/S WHT	16	2	0.178	REELEX	1000'	25	WHITE	CMP/CL3P
P50032.1D	57564203	16/2C STR BC N/S WHT	16	2	0.178	REELEX	500'	25	WHITE	CMP/CL3P
P50059.1A	57564302	16/4C STR BC N/S WHT	16	4	0.21	REELS	1000'	45	WHITE	CMP/CL3P
P60040.1A	57564402	14/2C STR BC N/S WHT	14	2	0.216	REELS	1000'	37	WHITE	CL3P/FPLP
P70031.1A	57786802	12/2C STR BC N/S WHT	12	2	0.264	REELS	1000'	56	WHITE	CL3P/FPLP



PLENUM RATED - EACH PAIR SHIELDED										
TWC PART NUMBER	SW PART NUMBER	DESCRIPTION	AWG	# PAIRS	NOM. DIAM. (inch)	PACKAGING			JACKET COLOR	UL/NEC®
						TYPE	LENGTH	lbs/1000 ft		
Burglar alarm, public address systems, intercoms, telephone stations, speakers, instrumentation & control, sunlight resistant. For all power-limited circuits use.										
P29691.1A	57577301	22/2P STR BC EPS WHT	22	2	0.148	REELS	1000'	21	WHITE	CMP/CL3P
P29841.1A	57721202	22/2P STR BC EPS (CD) WHT	22	2	0.148	REELS	1000'	18	WHITE	CMP/CL3P
P29841.1B	57721201	22/2P STR BC EPS (CD) WHT	22	2	0.148	REELEX	1000'	18	WHITE	CMP/CL3P
P29996.1A	57577501	22/3P STR BC EPS WHT	22	3	0.178	REELS	1000'	30	WHITE	CMP/CL3P
P49995.1A	57786502	18/2P STR BC EPS(CD) WHT	18	2	0.186	REELS	1000'	34	WHITE	CMP/CL3P