



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P442QT 2G PVC Flexbox *Allied Moulded Products*

Catalog Number	P442QT
Manufacturer	Allied Moulded Products
Description	Electrical Box, Polycarbonate;Carbon Steel (Fastener);Galvanized (Snap In Bracket) Material, Black, P-442 Model, 43.5 Cu.In Capacity, Clamp Cable Entry, 2 Gang, Rectangular, 1/2 In Knockout Size, 2 Knockouts, Angled Mid Nail, 4 In Length, 3-9/16 In Width, 3-3/4 In Height, 18 LB
Weight per unit	0.3400 (lbs/each)
Product Category	Non-Metallic

Features

Cable Entry	(2) 1/2 Inch Knockouts, Clamp
Device Mounting Holes	THREADED

Dimensions and Weight

Depth	3-9/16 INCH
Depth in inch	3 9/16
Height in inch	3 3/4 inches
Width in inch	4 in

Descriptions

Additional Information	WEIGHT 18 LB
Commodity Description	OUTLET BOXES - NON METALLIC
Description	2G PVC FLEXBOX

Manufacturer Information

Brand	Allied Moulded Products
GTIN	00085339440017
UPC	085339440017

Taxonomies, Classifications, and Categories

Category Description	PLASTIC BOXES
Type	GANGABLE

Packaging

Carton	48
Standard Package	50 A
Weight Per each	0.34

Uses, Certifications, and Standards

Approval	UL mA
Mounting	ANGLED NAIL

Two Gang:


Residential Switch or Receptacle Box

Series P-442



Cu. In. Volume	Catalog Number	Component Description	D	W	H	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
43.5	P-442*	Two gang, angled nails, molded-in Speed Klamps™	3-9/16	4	3-3/4	44000	50	18
43.5	P-442QT	Two gang, angled nails, Quick Thread™ device holes, molded-in Speed Klamps™	3-9/16	4	3-3/4	44001	50	18

Series P-442H



Cu. In. Volume	Catalog Number	Component Description	D	W	H	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
43.5	P-442H*	Two gang, face bracket side mount hanger, molded-in Speed Klamps™	3-9/16	4	3-3/4	44002	50	21
43.5	P-442HQT	Two gang, face bracket side mount hanger, Quick Thread™ device holes, molded-in Speed Klamps™	3-9/16	4	3-3/4	44003	50	21

P-240OW



Cu. In. Volume	Catalog Number	Component Description	D	W	H	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
40.0	P-240OW	Two gang, wing brackets, ears, molded-in Speed Klamps™, use LVP-2 partition for dual voltage applications	3-25/64	4-7/64	3-11/16	24912	24	11

Three Gang:


Residential Switch or Receptacle Box

Series P-643




Cu. In. Volume	Catalog Number	Component Description	D	W	H	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
64.0	P-643*	Three gang, angled nails, molded-in Speed Klamps™	3-9/16	5-13/16	3-3/4	46302	20	10
64.0	P-643QT	Three gang, angled nails, Quick Thread™ device holes, molded-in Speed Klamps™	3-9/16	5-13/16	3-3/4	46301	20	10

Series P-643H



Cu. In. Volume	Catalog Number	Component Description	D	W	H	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
64.0	P-643H*	Three gang, face bracket side mount hanger, molded-in Speed Klamps™	3-9/16	5-13/16	3-3/4	46303	20	11
64.0	P-643HQT	Three gang, face bracket side mount hanger, Quick Thread™ device holes, molded-in Speed Klamps™	3-9/16	5-13/16	3-3/4	46304	20	11

P-352OW



Cu. In. Volume	Catalog Number	Component Description	D	W	H	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
52.0	P-352OW	Three gang, wing brackets, ears, molded-in Speed Klamps™, use LVP-2 partition for dual voltage applications	3-25/64	5-59/64	3-11/16	33201	12	8

* Indicates model shown • See page 32 for Attachment Coding descriptions

