

Eaton P48G11S03P

Catalog Number: P48G11S03P

Eaton Mini-Power Center, Single-phase, PV: 480V, Taps: 2 at -5% FCBN, SV: 120/240V, 115°C, 3 kVA, Al windings , Frame: 283, Indoor-Outdoor.



Photo is representative

General specifications

Product Name

Eaton Mini-Power center

Catalog Number

P48G11S03P

UPC

786680140136

Product Length/Depth

8.9 in

Product Height

27.5 in

Product Width

11.9 in

Product Weight

130 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

NEMA Compliant

Certifications

UL Listed

ANSI

CSA Certified

IEEE Certified

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 3R

Frame

283

Tap size

2 at -5% FCBN

Type

Mini-power center

Wiring connection

97A3K

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

3 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - P48G11S03P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)