

# Eaton P48G11S0512

Catalog Number: P48G11S0512

5 KVA Mini Power Center 1PH 480V-120/240V 12 spaces



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Mini-Power center	P48G11S0512
UPC	Product Length/Depth
786680225536	8.9 in
Product Height	Product Width
29.5 in	11.9 in
Product Weight	Warranty
167 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
NAFTA	CSA Certified
	UL Listed
	ANSI
	IEEE Certified

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 3R

### Frame

284

### Insulation

180 °C

### Mounting

Wall Mount

### Tap size

2 at -5% FCBN

### Type

Mini-power center

### Wiring connection

M48G11D

## Performance Ratings

### Frequency rating

60 Hz

### kVA

5 kVA

### Kva Rating

5 kVA

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Sound Level

NEMA ST-20

### Temperature rise

115 °C rise

### Volt ampere rating

5 kVA

## Miscellaneous

### Modification 1

NEMA 3R

### Weathershield

Not required

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - P48G11S0512](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)