DATE: TYPE:

NAME:

PROJECT:



Incandescent

P4961-30

Square Glass

White glass.

Diameter: 12”
Height: 5-1/2”

Category: Close-to-Ceiling
Finish: White
Construction: Steel construction
Glass: White glass

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Canopy covers a standard 4” hexagonal recessed outlet box 4-3/8” dia.	Pre-wired 6” of wire supplied 120V	Quantity: 2 60W Medium Base Medium porcelain sockets	UL-CUL Dry location listed 1 year warranty Companion fixtures are available

DATE: TYPE:

NAME:

PROJECT:



Incandescent

P4961-30

Square Glass

White glass.

Diameter: 12”
Height: 5-1/2”

Category: Close-to-Ceiling
Finish: White
Construction: Steel construction
Glass: White glass

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Canopy covers a standard 4” hexagonal recessed outlet box 4-3/8” dia.	Pre-wired 6” of wire supplied 120V	Quantity: 2 60W Medium Base Medium porcelain sockets	UL-CUL Dry location listed 1 year warranty Companion fixtures are available