

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P5131-09

Heart

One-light Brushed Nickel mini-pendant with etched glass shade.

- Plated Brushed Nickel finish.
- Etched glass shades provide satisfying illumination.
- Versatile design.
- Includes two 6" stems and 42 in of chain.

Category: Pendants

Finish: Brushed Nickel (Plated)
Construction: Steel construction
Glass/Shade: Etched glass shade



Diameter: 5-13/16"

Height: 6"

Overall Ht. W/Chain Or Stem: 64"

Glass

Width: 5-3/4" Height: 4-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included 42 in of 9 gauge chain supplied Two 6" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 0.9375" depth	Pre-wired 8 feet of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base ceramic socket	UL-CUL Dry location listed 1 year warranty
3.125 W., 6.3373 depar			