



P8A

by Burndy
Catalog ID: P8A

Penetrox Bottle ,5.80 in Length ,2.04 in Width.

consists of a natural (petroleum) base vehicle in which zinc particles are suspended

Product Details

General

Application	Aluminum to Aluminum, Aluminum to Conduit,Aluminum to Copper
Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Squeeze Bottle
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592557
UPC 12 Digit	7818105925577
Viscosity at 100 Fahrenheit	305 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	8 oz
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)