

PAR20-7-930-40D-DIM



Project:

Type:

Prepared By:

Date:



UPC: 019813749464



Features and Benefits

Produces rich and vibrant colors >90CRI

Energy efficient replacement for incandescent and halogen PAR lamps

Constructed from durable materials which lowers risk of breakage

Rated for use in enclosed and open fixtures in dry and damp locations*

Single optic and full face lens for precise beam angle control

Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs

Title 20 Compliant, ENERGY STAR Compliant, UL Listed

Dimmable down to 10% (check dimmer compatibility list)

*PAR38 is wet rated

Technical Specifications

Performance

Product Type:

PAR

Input Wattage:

7W

Typical Lumen Output:

550

Efficacy:

79 lm/W

Color Temperature:

3000K Warm White

CRI:

90

L70 Lifespan:

40,000 Hours

Dimmable:

Yes, down to 10%

Construction

Bulb Shape:

PAR20

Base Type:

E26

Beam Angle:

40°

Other

Equivalency:

50W Halogen

Warranty (Years):

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of four (4) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Electrical

Power Factor:

0.9

Operating Temperature:

-20°C - 45°C

Input Voltage:

120V

Technical Specifications

For Use Outdoors in Open Fixtures:

No

PAR20-7-930-40D-DIM



Technical Specifications (continued)

Electrical Characteristics

Flicker:

<30%

Compliance

UL Listed:

Yes

ENERGY STAR V2.0:

This product is ENERGY STAR® Version 2.0 Certified

Energy Star ID:

2329948


CEC Status:

Lawful for sale in California

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	12	10.8	8.1	4.1
PALLET	2880	43.2	37.9	48.7

Dimension



Light Distribution

