



Project:

Type:

Prepared By:

Date:



UPC: 019813749969

Features and Benefits

- Energy efficient replacement for incandescent and halogen PAR lamps
- Constructed from durable materials which lowers risk of breakage
- Rated for use in enclosed and open fixtures in wet locations
- Single optic and full face lens for precise beam angle control
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- Replacements for halogen PAR lamps. Dimmable LED with 80 CRI and wet rated, great for use outdoors.

Technical Specifications

Performance

Product Type:
PAR

Input Wattage:
15W

Lumens:
1,050lm

Efficacy:
70lm/W

L70 Lifespan:
25,000 Hours

Construction

Shape:
PAR38

For Use Outdoors in Open Fixtures:
Yes

LED Characteristics

Color Temperature:
4000K Cool White

Color Accuracy (CRI):
80 CRI

Beam Angle:
40°

Installation

Base Type:
E26 Edison

Electrical

Power Factor:
0.7

Operating Temperature:
-20°C to 45°C (-4°F to 113°F)

Dimmable:
Yes, down to 20%

Input Voltage:
120V

Flicker:
<30%

Other

4-Year, No-Compromise Warranty:
RAB warrants that our LED products will be free from defects in materials and workmanship for a period of four (4) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Compliance

UL Listed:
Yes

Energy Star Approved:
This product is ENERGY STAR® Version 2.0 Certified

Energy Star ID:
2330085


California Energy Commission (CEC) Status:
Not Lawful for Sales in California




Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	6	15.1	10.2	6
PALLET	360	45.4	35.5	48.5

Dimension



Light Distribution





Project:

Type:

Prepared By:

Date:



UPC: 019813749969

Features and Benefits

- Energy efficient replacement for incandescent and halogen PAR lamps
- Constructed from durable materials which lowers risk of breakage
- Rated for use in enclosed and open fixtures in wet locations
- Single optic and full face lens for precise beam angle control
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- Replacements for halogen PAR lamps. Dimmable LED with 80 CRI and wet rated, great for use outdoors.

Technical Specifications

Performance

Product Type:
PAR

Input Wattage:
15W

Lumens:
1,050lm

Efficacy:
70lm/W

L70 Lifespan:
25,000 Hours

Construction

Shape:
PAR38

For Use Outdoors in Open Fixtures:
Yes

LED Characteristics

Color Temperature:
4000K Cool White

Color Accuracy (CRI):
80 CRI

Beam Angle:
40°

Installation

Base Type:
E26 Edison

Electrical

Power Factor:
0.7

Operating Temperature:
-20°C to 45°C (-4°F to 113°F)

Dimmable:
Yes, down to 20%

Input Voltage:
120V

Flicker:
<30%

Other

4-Year, No-Compromise Warranty:
RAB warrants that our LED products will be free from defects in materials and workmanship for a period of four (4) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Compliance

UL Listed:
Yes

Energy Star Approved:
This product is ENERGY STAR® Version 2.0 Certified

Energy Star ID:
2330085

California Energy Commission (CEC) Status:
Not Lawful for Sales in California


PAR38-15-840-40D-DIM



Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	6	15.1	10.2	6
PALLET	360	45.4	35.5	48.5

Dimension



Light Distribution

