

by Wiegmann Catalog ID: PB1

N4 30.5 MM 1 Pushbutton Enclosure 3.5X3.2X2.7 Carbon Steel - Gray

• Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

Product Details

General

Application	Designed to hold all standard brands of pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Pushbutton;Screw
Finish Type	Polyester Powder
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Number of Holes	1
Series	РВ
Туре	Standard Pushbutton Enclosure
UPC	786725430055

Dimensions

Actual Depth	3.5 in
Actual Height	3.500 in
Actual Width	3.250 in
Depth	4 in
Height	4 in

Weight	1.67 lb	
Width	3 in	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	4	
UL Listed	Yes	