

by Wiegmann Catalog ID: PB2

N4 30.5 MM 2 Pushbutton Enclosure 5.7X3.2X2.7 Carbon Steel - Gray

• Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

Product Details

General

Designed to hold all standard brands of pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil and water.
Gray
Continuously Welded Seams
Pushbutton;Screw
Polyester Powder
UL, CSA
Carbon Steel
External Mounting Plates
Wall Mount
2
РВ
Standard Pushbutton Enclosure
786725430109

Dimensions

Actual Depth	5.750 in
Actual Height	5.750 in
Actual Length	5.75 in
Actual Width	3.250 in
Depth	6 in

Height	6 in	
Weight	2.5 lb	
Width	3 in	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	4	
UL Listed	Yes	