

PVC Coated Elbows

3X45 PVC COATED STANDARD ELBOW



Catalog Number	PRHELB-3X45
UPC	784011200429

Description

Factory-bent PVC coated elbows are more accurate, quicker to install and more economical because they eliminate field bending time and waste of material. Electrical continuity is maintained across assembled joints.

Application

- Factory-bent for accurate, quicker to install and eliminates costly field bending and waste of material

Features


- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- 12 trade sizes from 1/2" through 6"
- Available in standard sizes 90°, 60°, 45°, 30° bends
- Color-coded thread protector caps for quick identification of conduit size

General Information

Trade Size	3
Material	STEEL
Material	STEEL
Exterior Finish	A nominal .040 inch (40 mil) gray PVC coating
Interior Finish	A nominal .002 inch (2 mil) red urethane
Thread Finish	A red urethane coating over steel
Thread Protector Color	Blue

Dimensions

Diameter - External (Inches)	3.58
------------------------------	------



Diameter - Internal (Inches)	3.08
Metric Size Designators	78
Nipple Length (Inches)	32
Offset D (Inches)	17
Offset E (Inches)	18.79
Offset F (Inches)	20.58
Radius A (Inches)	11.21
Radius B - Standard (Inches)	13
Radius C (Inches)	14.79
Tangent (Inches)	5.79



Standards

CSA Certified	C22.2 No. 45
UL 6	E2314

Technical Specification Documents

Specification Guide (1995 Master)	AVAILABLE ON WEBSITE
Specification Guide (2004 Master)	AVAILABLE ON WEBSITE
Installer Certification and Tools	AVAILABLE ON WEBSITE
Chemical Resistance Charts	AVAILABLE ON WEBSITE
Performance Specifications	AVAILABLE ON WEBSITE

Technical Information

Fitting Configuration	45
Fitting Type	STANDARD RADIUS ELBOW
Product Category	ELBOW
Product Family	PVC Coated Elbows

Notes

- Both PVC and zinc coatings have been investigated as primary protection against corrosion.
- Restricted for use with threaded fittings only.