

Eaton PFMA11LCY-UNV1-76

Catalog Number: PFMA11LCY-UNV1-76

Eaton Crouse-Hinds series Champ Pro PFMA LED floodlight, Cool white, Dimmable driver, 3/4" entry, 250-400W equiv, Heat and impact resistant glass lens, 11000 lumens, 135 lm/W, Die cast alum, Yoke mt, 100-277 Vac, 108-250 Vdc, 82W, 7x6 optic

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Champ Pro PFMA LED floodlight	PFMA11LCY-UNV1-76
	UPC
	662276873490
Product Length/Depth	Product Height
15.5 in	12 in
Product Width	Product Weight
7 in	31.8 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

IEC

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lamp type

LED

Lumens

11000

Lumens per watt

135

Color temperature

Cool white

Mounting Method

Yoke

Voltage rating

100-277 Vac, 108-250 Vdc

Frequency rating

50/60 Hz

Optical distribution

7x6

Entry size

3/4"

Lens material

Heat and impact resistant glass

Wattage

82W

Dimming

Dimmable driver

Equivalent luminaire

250-400W

Power factor

> 0.90

Material

Die cast aluminum

Resources

[3D models](#)

SP3D Design Package - Champ Pro PFMA LED Industrial Floodlights

Brochures

Crouse-Hinds series Global LED lighting portfolio

Crouse-Hinds series DLC approved lighting products

Crouse-Hinds series Champ PFMA LED Floodlights - 9,000 to 15,000 lumens brochure

Crouse-Hinds series industrial LED lighting solutions

Catalogs

Crouse-Hinds series Champ PFMA LED Floodlights - 9,000 to 15,000 lumens catalog page

Certification reports

Champ PFMA LED Floodlights ABS certification

Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures UL certification

Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures Canadian certification

Installation instructions

IF 1891 - Champ LED Floodlight PFMA

Specifications and datasheets

Eaton Specification Sheet - PFMA11LCY-UNV1-76



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia