

Eaton PFME30LCY-UNV1-66

Catalog Number: PFME30LCY-UNV1-66

Eaton Crouse-Hinds series PFME LED floodlight, Cool white, Dimmable driver, 750W-1000W HID equivalent, 50/60 Hz, Polycarbonate lens, 30000 lumens, 127 lm/W, Aluminum, Yoke mount, Standard 120° angle, >0.90 PF, 120-277 Vac, 127-400 Vdc, 242W

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PFME LED floodlight	PFME30LCY-UNV1-66
	UPC
	662276966826
Product Length/Depth	Product Height
20.16 in	12.5 in
Product Width	Product Weight
4.17 in	35.64 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Lamp type

LED

Lumens

30000

Lumens per watt

127

Color temperature

Cool white

Mounting Method

Yoke

Voltage rating

120-277 Vac, 127-400 Vdc

Frequency rating

50/60 Hz

Optical distribution

Standard 120° angle

Dimming

Dimmable driver

Wattage

242W

Equivalent luminaire

750W-1000W HID

Power factor

> 0.90

Material

Aluminum

Lens material

Polycarbonate

Resources

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds PFME LED Floodlights brochure](#)

Catalogs

[Crouse-Hinds PFME LED Floodlights catalog page](#)

Installation instructions

[IF 1926 - PFME Industrial LED Floodlight](#)

Specifications and datasheets

[Eaton Specification Sheet - PFME30LCY-UNV1-66](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia