



## Cover, Polymer Concrete, Tier 15, 24"x36"

By QUAZITE  
Catalog # [PG2436HA0009](#)

Quazite ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.



\*Representative Image

### Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
UPC	662037100537
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Dimensions	36 in x 24 in x 3 in
Height	3 in
Length	36 in
Weight	112 lb
Width	24 in

### Product Assets

[Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)  
[Literature - Quazite® FRP Cover Options \(Logos\)](#)  
[Sales Drawings - Quazite Cover Standard Version \(PG2436HA00\)](#)  
[Video - PenCell® How It's Made \(VI07068E0617\)](#)  
[Video - PenCell® Enclosures \(VI07062E0617\)](#)  
[Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
QUAZ-PG2436HA0009-SPEC-EN | REV 9/2023