



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PJS262V Wallplate 2G Deco Screwless Poly Mid Iv

Eaton Wiring Devices

Catalog Number	PJS262V
Manufacturer	Eaton Wiring Devices
Description	Eaton Screwless Wallplate, Screwless, Ivory, Decorator Cutout, Polycarbonate, Two- Gang, Mid-Size
Weight per unit	0.1280 (lbs/each)
Product Category	Wall Plates & Covers

Features

amperage rating	N/A
dimensions	0.0800 IN X 4.9400 IN X 4.8700 IN
Voltage Rating	N/A

Material, Color, and Finish

Style	(blank)
-------	---------

Dimensions and Weight

Size	4.875 IN Length 4.95 IN Width 0.5 IN Height
------	---

Descriptions

Description	WALLPLATE 2G DECO SCREWLESS POLY MID IV
extra long description	EWD PJS262V Wallplate 2G Deco Screw
Features	Eaton's broad offering of wallplates are the final touch for any application and are available in standard size, mid-size and oversize. Upgrade your home with screwless wallplates which provide a clean, seamless look. Choose from a variety of materials, colors, and configurations to match any combination of device and décor. Weather protective covers are available in a wide selection of configurations to maintain the integrity of outdoor devices.
Long Description	Eaton Screwless wallplate, Screwless, Ivory, Decorator Cutout, Polycarbonate, Two- gang, Mid-size
Product Type	Wallplate 2G Deco Screwless Poly Mid Iv
Special Features	Screwless Wallplates clip easily into place with gentle pressure

Manufacturer Information

Brand	Eaton
GTIN	00032664750977
Manufacturers Part Number	PJS262V
UPC	032664750977

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Wallplates



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Weight Per each	0.128

Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	UL94