



6
INCH
DIAMETER



QL07/120

Descript.: For new construction. Thermally protected, labor saving, recessed housing. Engineered polymer plaster frame includes pre-positioned nails for fast installation. Adjustable socket mounting plate. Four Romex knockouts and two 1/2" conduit knockouts. Uses 13 watt CFQ13W/GX23 fluorescent lamp, not included. Standard in 120V Normal Power Factor. U.L. listed for Damp Locations and Through-Branch Circuit Wiring. Height: 7 1/2" (191 mm), Length: 14 1/4" (362 mm), Width: 8 1/2" (216 mm), Ceiling Opening: 6 1/4" (159 mm)

Std. Pack: 6
Ship Wt.: 19




PL07/120 **QS**

PL07/120HPF

PL07/277HPF

Descript.: For new construction. Thermally protected, recessed housing. Includes BH6 SURE-LOK® bar hangers and adjustable socket mounting plate. Remodel capability. Five 1/2" conduit knockouts and 4 Romex knockouts. Uses 13 watt CFQ13W/GX23 fluorescent lamp, not included. Standard in 120V Normal Power Factor. U.L. listed for Damp Locations and Through-Branch Circuit Wiring. Height: 7 1/2" (190 mm), Length: 12 1/2" (318 mm), Width: 7 3/4" (197 mm), Ceiling Opening: 6 1/4" (159 mm)

Std. Pack: 6
Ship Wt.: 32




PL071C/120 **CS**

Descript.: Insulated ceiling housing. Uses 13 watt CFQ13W/GX23 fluorescent lamp, not included. For use in direct contact with thermal insulation. Pre-installed BH6 bar hangers for use in joists 16" to 24" (406 mm to 610 mm) on center. Standard in 120V Normal Power Factor. U.L. listed for Damp Locations and Through-Branch Circuit Wiring. Height: 7 3/4" (197 mm), Length: 12 1/2" (318 mm), Width: 7 3/4" (197 mm), Ceiling Opening: 6 1/4"

Std. Pack: 4
Ship Wt.: 28

PL07ASIC/120

Descript.: Air Seal™ IC rated housing. Same features as PL071C/120 above. Sealed to prevent passage of air to/from the ceiling plenum. Meets all WSEC requirements.



PLR07/120

PLR07/120HPF

Descript.: Remodel housing. Uses 13 watt CFQ13W/GX23 fluorescent lamp, not included. For installation in existing finished ceilings. Pre-installed clips secure the housing firmly into the ceiling. Use in ceiling thicknesses from 1/4" to 1 1/4" (6 mm to 32 mm). Standard in 120V Normal Power Factor. U.L. listed for Damp Locations and Through-Branch Circuit Wiring. Height: 7 3/4" (197 mm), Length: 14" (355 mm), Width: 6 1/4" (159 mm), Ceiling Opening: 6 1/4" (159 mm)

Std. Pack: 6
Ship Wt.: 15

OPTIONS

- BH3** Pair 27" (686 mm) Flat Bar Hangers.
- RF** Radio Interference Filter.

Note: **QS** Quick Ship products are normally stocked at the factory and available for immediate shipment.