




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLF1MAM4Y Mini-MRKR Tie Bulk Panduit Corporation

Catalog Number	PLF1MAM4Y
Manufacturer	Panduit Corporation
Description	
Weight per unit	2.0 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Bundle Diameter	0.87 IN
Material	Nylon 6-6
Tensile Strength	51330

Material, Color, and Finish

Color	Yellow Handle
-------	---------------

Dimensions and Weight

Length	CR411E205H21AAAAA
Thickness	50 MM (STATIC), 120 MM (DYNAMIC)
Width	DIMMING LINEAR FLUORESCENT BALLAST, 9.5 INCH L X 1.71 INCH W X 1.2 INCH D SIZE; 50 DEG F MIN. STARTING TEMPERATURE; 10 PERCENT MAX. THD; 50/60 HZ FREQUENCY RATING; UL, CSA APPROVAL; 1 LAMP(S); T8 LAMP TYPE; 32 W LAMP WATTAGE; 120/277 VAC INPUT VOLTAGE

Descriptions

Description	MINI-MRKR TIE BULK
Product Type	Markertie, Flag, Min, 5.1IN, Y, PK1000
Special Features	Indoor

Manufacturer Information

Brand	PANDUIT CORPORATION
GTIN	00074983445868
Manufacturers Part Number	PLF1MA-M4Y
sub brand	Pan-Ty
UPC	074983445868

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Cable Ties



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685


Packaging

Carton	5000
Package	10
Weight Per each	2

Uses, Certifications, and Standards

Application	General
standard	UL Compliant 62275, UL Listed #E56854, UL Recognized #E56854

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	J	WRITE-ON AREA IN. (mm)	MINIMUM LOOP TENSILE lbs. (N)	CROSS-SECTION	WEIGHT LBS/100 (G)
	MIN. IN. (mm)	MAX. IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)				
PLF 1M	.06 (1.5)	.87 (22.1)	.045 (1.1)	.098 (2.5)	.177 (4.5)	.154 (3.9)	.180 (4.6)	4.3 (109)	.812 (20.6)	.366 (9.3)	.028 (.71)	.31 X .75 (7.9 X 19.1)	18 (80)	MINIATURE	.10 (46)
PLF 1MA	.06 (1.5)	.87 (22.1)	.045 (1.1)	.098 (2.5)	.177 (4.5)	.154 (3.9)	.180 (4.6)	5.1 (130)	.812 (20.6)	1.10 (28.)	.028 (.71)	.76 X 1.04 (19.1 X 26.4)	18 (80)	MINIATURE	.16 (73)
PLF 1MB	.06 (1.5)	.75 (19)	.045 (1.1)	.098 (2.5)	.177 (4.5)	.154 (3.9)	.180 (4.6)	3.98 (101)	.980 (24.9)	.366 (9.3)	.028 (.71)	.31 X .92 (7.9 X 23.4)	18 (80)	MINIATURE	.10 (46)

NOTES:

- * SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS						
										<p>PANDUIT CORP. TINLEY PARK, ILLINOIS</p> <p>PAN-TY® FLAG MARKER TIE</p> <p>PLF SERIES</p>						
										<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .005 (.127) (.XXX) ± .020 (.51) (.XX) ± .02 (.51) ANGLES ± .005</p>						
										<p>UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.</p>						
										<p>DRAWN BY L.V./AJC</p>		<p>MAT'L: NYLON 6/6</p>		<p>SCALE NONE</p>		
										<p>DATE 2-10-71</p>		<p>DRAWING NO. SS-2723</p>		<p>DWG A SIZE</p>		
										<p>CHK'D HVP</p>						
11	2/13/03	JABO		ADDED WRITE-ON AREA FOR ALL PARTS				2723	11							
REV	DATE	BY	CHK	DESCRIPTION				ECN - R	CUST	SUP						