



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1010FD 12-10AWG #10STD Nylon Insld Fork TRML *Panduit Corporation*

Catalog Number	PN1010FD
Manufacturer	Panduit Corporation
Description	Fork Terminal, Nylon Insulated, 12- 10 Awg, #10 Stud Size, Bulk Package.
Weight per unit	0.0051 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	12-10AWG #10STD NYLON INSLTD FORK TRML
extra long description	PAN PN10-10F-D Pan-Term® PN10-10F-D
Long Description	Fork Terminal, nylon insulated, 12- 10 AWG, #10 stud size, bulk package.
Product Type	Pan-Term® PN10-10F-D Loose Piece Forks

Manufacturer Information

Brand	Panduit®
GTIN	00074983803217
Manufacturers Part Number	PN10-10F-D
UPC	074983803217

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal

Availability

minimum qty	500
-------------	-----

Packaging

Carton	500
Weight Per each	0.0051



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	9/32
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)