



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1038RD 12-10AWG 3/8"STD Ylw Nyl Insltd Ring TRML

Panduit Corporation

Catalog Number	PN1038RD
Manufacturer	Panduit Corporation
Description	Ring Terminal, 12 – 10 Awg, 3/8" Stud Size, Nylon Insulated, Bulk Package.
Weight per unit	0.0062 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	3/8"
------	------

Descriptions

Description	12-10AWG 3/8"STD YLW NYL INSLTD RING TRML
extra long description	PAN PN10-38R-D Pan-Term® PN10-38R-D
Long Description	Ring Terminal, 12 – 10 AWG, 3/8" stud size, nylon insulated, bulk package.
Product Type	Pan-Term® PN10-38R-D Ring Terminal

Manufacturer Information

Brand	Panduit®
GTIN	00074983800391
Manufacturers Part Number	PN10-38R-D
UPC	074983800391

Taxonomies, Classifications, and Categories

Type	Ring Terminal
------	---------------

Availability

minimum qty	500
-------------	-----

Packaging

Carton	500
Weight Per each	0.0062



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Ring shape
Mounting	9/32
standard	UL Listed 587H E52164, CSA Certified LR31212, Military QPL AS7928 (MS25036-114)
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)