



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005



PN1438RM 18-14AWG 3/8"STD Nylon Insltd Ring TRML *Panduit Corporation*

Catalog Number	PN1438RM
Manufacturer	Panduit Corporation
Description	Ring Terminal, 18 – 14 Awg, 3/8" Stud Size, Nylon Insulated, Bulk Package.
Weight per unit	0.0030 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	3/8"
------	------

Descriptions

Description	18-14AWG 3/8"STD NYLON INSLTD RING TRML
extra long description	PAN PN14-38R-M Pan-Term® PN14-38R-M
Long Description	Ring Terminal, 18 – 14 AWG, 3/8" stud size, nylon insulated, bulk package.
Product Type	Pan-Term® PN14-38R-M Loose Piece Ring Terminal

Manufacturer Information

Brand	Panduit®
GTIN	00074983800278
Manufacturers Part Number	PN14-38R-M
UPC	074983800278

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	0.003



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005

Uses, Certifications, and Standards

Enclosure	Ring shape
Mounting standard	7/32 UL Listed 587H E52164, CSA Certified LR31212, Military QPL AS7928 (MS25036-110)
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)