



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN146FM 14-16AWG #6STD Nylon Insld Fork TRML *Panduit Corporation*

Catalog Number	PN146FM
Manufacturer	Panduit Corporation
Description	Fork Terminal, Nylon Insulated, 16- 14 Awg, #6 Stud Size, Bulk Package.
Weight per unit	0.0004 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#6
------	----

Descriptions

Description	14-16AWG #6STD NYLON INSLTD FORK TRML
extra long description	PAN PN14-6F-M Pan-Term® PN14-6F-M F
Long Description	Fork Terminal, nylon insulated, 16- 14 AWG, #6 stud size, bulk package.
Product Type	Pan-Term® PN14-6F-M Fork Terminal, Blue, Nylon, 14-16 Awg, #

Manufacturer Information

Brand	Panduit®
GTIN	00074983803095
Manufacturers Part Number	PN14-6F-M
UPC	074983803095

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	0.0004



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	7/32
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)