



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street  
74701-0000, OK Durant  
Phone: 580-745-5448  
Fax: 580-745-5449



## PN148RM 18-14AWG #8STD Nylon Insld Ring TRML *Panduit Corporation*

Catalog Number	PN148RM
Manufacturer	Panduit Corporation
Description	The PN14-8R-M Pan-Term® Terminal Is A Nylon Insulated, Ring Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0024 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Standard
insulation	Nylon
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	14

### Material, Color, and Finish

Color	Blue
Finish	Tinned

### Dimensions and Weight

Size	#8
------	----

### Descriptions

Description	18-14AWG #8STD NYLON INSLTD RING TRML
extra long description	PAN PN14-8R-M Pan-Term® PN14-8R-M R
Long Description	The PN14-8R-M Pan-Term® Terminal is a nylon insulated, ring terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN14-8R-M Ring Terminal, Blue, Nylon, 14-18 Awg, #

### Manufacturer Information

Brand	Panduit®
GTIN	00074983800193
Manufacturers Part Number	PN14-8R-M
UPC	074983800193



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street  
74701-0000, OK Durant  
Phone: 580-745-5448  
Fax: 580-745-5449

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Ring Terminal

## Availability

minimum qty ..... 1000

## Packaging

Carton ..... 1000

Weight Per each ..... 0.0024

## Uses, Certifications, and Standards

Enclosure ..... Ring shape

Mounting ..... 7/32

standard ..... cULus Listed 587H E52164, CSA Certified LR31212, Military QPL  
AS7928 (MS25036-153)

Temperature Rating ..... 221 Degrees Fahrenheit (105 Degrees Celsius)