



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St  
72762-0000, AR Springdale  
Phone: 479-361-2266  
Fax: 479-361-9188



## PN1810FC #18 Nyl FK Term *Panduit Corporation*

Catalog Number	PN1810FC
Manufacturer	Panduit Corporation
Description	Fork Terminal, Nylon Insulated, 22- 18 Awg, #10 Stud Size, Standard Package.
Weight per unit	0.0006 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	18

### Material, Color, and Finish

Color	Red
Finish	Tinned

### Dimensions and Weight

Size	#10
------	-----

### Descriptions

Description	#18 NYL FK TERM
extra long description	PAN PN18-10F-C Pan-Term® PN18-10F-C
Long Description	Fork Terminal, nylon insulated, 22- 18 AWG, #10 stud size, standard package.
Product Type	Pan-Term® PN18-10F-C Loose Piece Forks

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983803040
Manufacturers Part Number	PN1810FC
UPC	074983803040

### Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal

### Packaging

Carton	100
Weight Per each	0.0006



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St  
72762-0000, AR Springdale  
Phone: 479-361-2266  
Fax: 479-361-9188

## Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	7/32
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)