



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604



PNF1410FC Pan-Term® PNF14-10F-C Loo Panduit Corporation

Catalog Number	PNF1410FC
Manufacturer	Panduit Corporation
Description	Fork Terminal, Nylon Insulated, Funnel Entry, 16- 14 Awg, #10 Stud Size, Standard Package.
Weight per unit	0.5600 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	PAN-TERM® PNF14-10F-C LOO
extra long description	PAN PNF14-10F-C Pan-Term® PNF14-10F
Long Description	Fork Terminal, nylon insulated, funnel entry, 16- 14 AWG, #10 stud size, standard package.
Product Type	Pan-Term® PNF14-10F-C Loose Piece Terminal

Manufacturer Information

Brand	Panduit®
GTIN	00074983513529
Manufacturers Part Number	PNF14-10F-C
UPC	074983513529

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal

Packaging

Carton	100
Package	500
Weight Per each	0.56



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	5/16
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)