



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS15AC1I 15A 1P Spec SW *Pass & Seymour/Legrand*

Catalog Number	PS15AC1I
Manufacturer	Pass & Seymour/Legrand
Description	
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Switches

### Features

actuator	Toggle
amperage rating	15 A
Contact Rating	15Amp, 120/277V
insulation	None IN
Poles	1 PH
Voltage Rating	120/277 VAC

### Material, Color, and Finish

Color	IVORY
-------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	15A 1P SPEC SW
Product Type	15A 120/277VAC B+S Wire SP SW
Special Features	Heavy duty switch, back & side wire, shallow design for ease of installation

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007196528
Manufacturers Part Number	PS15AC1-I
sub brand	Pass & Seymour
UPC	785007196528

### Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

### Packaging

Carton	10
Package	50
Weight Per each	0.2



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	COMMERCIAL/RESIDENTIAL
Mounting	WALL
standard	UL20



## INDUSTRIAL EXTRA HEAVY-DUTY SPECIFICATION GRADE SWITCH, IVORY

PS15AC11 | [Pass & Seymour](#)

### FEATURES & BENEFITS

1pole Toggle Switch, Back & Side Wire, 15amp 120/277volt, Ivory

- One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.
- Impact- and chemical-resistant cover.
- Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.
- One-piece nickel-plated brass strap for superior corrosion-resistance.
- Auto-ground clip assures positive ground.
- Cam control and spring actuator for positive "makes and breaks."
- Heavy-duty bumpers for quiet, smooth operation.
- Locking support provides resistance to face and back body separation.
- Oversized silver-alloy contacts for long life and better heat dissipation.
- Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.
- Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.
- Grounding terminal is standard with screw-pressure plate back wire.
- Shallow design for easier installation.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Type: Toggle  
Duty: Extra Heavy Duty  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

## DIMENSIONS

Depth (US): 1.073"

Height (US): 3.281"

Width (US): 1.320"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC

Volts (AC): 120/277

Grade Type: Industrial

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

