



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS20AC1KL 20A 120/277VAC B+S Wire SP Key Lock SW

*Pass & Seymour/Legrand*

Catalog Number	PS20AC1KL
Manufacturer	Pass & Seymour/Legrand
Description	1-Pole Key Lock Back and Side-Wire 20A 120/277V
Weight per unit	0.2237 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SP
actuator	Toggle
amperage rating	20
Contact Rating	20Amp, 120/277V
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	CFL, Incandescent, Universal, Halogen, LED, Fluorescent, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120.0 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE SP KEY LOCK SW
extra long description	P&S PS20AC1KL 20A 120/277VAC B+S WI
Features	Chemical Resistant
Long Description	1-Pole Key Lock Back and Side-Wire 20A 120/277V
Product Type	20A 120/277VAC B+S Wire SP Key Lock SW
Special Features	Heavy duty switch, back & side wire, shallow design for ease of installation with Key lock



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195651
Manufacturers Part Number	PS20AC1-KL
UPC	785007195651

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.2237

## Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL FEDSPEC, CULUS, UL20, FEDSPEC