



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS20AC3BK 20A 120/277VAC B+S Wire 3W SW BK

*Pass & Seymour/Legrand*

Catalog Number	PS20AC3BK
Manufacturer	Pass & Seymour/Legrand
Description	3-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2240 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	LED, Incandescent, Halogen, Xenon, Universal, CFL, Fluorescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	277 VAC, 120 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	3
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE 3W SW BK
extra long description	P&S PS20AC3BK 20A 120/277VAC B+S WI
Features	Chemical Resistant
Long Description	3-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire 3W SW BK
Special Features	High strength toggle, heavy duty toggle bumpers, locking support



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007195378
Manufacturers Part Number	PS20AC3-BK
UPC	785007195378

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.224

## Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL FEDSPEC, CULUS, UL 20, FEDSPEC