



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC3WL 20A 120/277VAC B+S Wire 3W Lock SW WH

Pass & Seymour/Legrand

Catalog Number	PS20AC3WL
Manufacturer	Pass & Seymour/Legrand
Description	3-Way Lock Switch, Back and Side-Wire, 20A 120/277V (Key Can Be Removed In Both Positions)
Weight per unit	0.2240 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Fluorescent, Universal, CFL, Incandescent, LED, Xenon, Halogen
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	3
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	20A 120/277VAC B+S WIRE 3W LOCK SW WH
extra long description	P&S PS20AC3WL 20A 120/277VAC B+S WI
Features	Chemical Resistant
Long Description	3-Way Lock Switch, Back and Side-Wire, 20A 120/277V (Key can be removed in both positions)
Product Type	20A 120/277VAC B+S Wire 3W Lock SW W
Special Features	High strength toggle, heavy duty toggle bumpers, locking support



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007196481
Manufacturers Part Number	PS20AC3-WL
UPC	785007196481

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.224

Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL FEDSPEC, CULUS, UL 20, FEDSPEC