



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1207 Energy Drive  
75662-0000, TX Kilgore  
Phone: 903-984-8485  
Fax: 903-984-8193



## PS20AC4GRY 20A 120/277VAC B+S Wire 4W SW Gy

*Pass & Seymour/Legrand*

Catalog Number	PS20AC4GRY
Manufacturer	Pass & Seymour/Legrand
Description	4-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2260 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	4P
actuator	Toggle
amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Incandescent, Halogen, Universal, Fluorescent, LED, Xenon, CFL
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE 4W SW GY
extra long description	P&S PS20AC4GRY 20A 120/277VAC B+S W
Features	Chemical Resistant
Long Description	4-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire 4W SW Gry
Special Features	Heavy duty switch, back & side wire, with lock



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1207 Energy Drive  
75662-0000, TX Kilgore  
Phone: 903-984-8485  
Fax: 903-984-8193

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195477
Manufacturers Part Number	PS20AC4-GRY
UPC	785007195477

## Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.226

## Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL CSA, UL, CULUS, FEDSPEC, UL20, FEDSPEC