



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell
88101-0000, NM Clovis
Phone: 575-742-2504
Fax: 575-742-2508



PS20AC4IL 20A 120/277VAC B+S Wire 4W Lock SW Iv

Pass & Seymour/Legrand

Catalog Number	PS20AC4IL
Manufacturer	Pass & Seymour/Legrand
Description	4-Way Lock Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2260 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	CFL, LED, Halogen, Fluorescent, Xenon, Incandescent, Universal
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	4
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	20A 120/277VAC B+S WIRE 4W LOCK SW IV
extra long description	P&S PS20AC4IL 20A 120/277VAC B+S WI
Features	Chemical Resistant
Long Description	4-Way Lock Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire 4W Lock SW I
Special Features	High strength toggle, heavy duty toggle bumpers, locking support



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell
88101-0000, NM Clovis
Phone: 575-742-2504
Fax: 575-742-2508

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007266771
Manufacturers Part Number	PS20AC4-IL
UPC	785007266771

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.226

Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL FEDSPEC, UL, CSA, CULUS, UL 20, FEDSPEC