



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS30AC2 30A 120/277VAC B+S Wire DP SW BN

Pass & Seymour/Legrand

Catalog Number	PS30AC2
Manufacturer	Pass & Seymour/Legrand
Description	2-Pole Toggle Switch, Back and Side-Wire, 30A 120/277V
Weight per unit	0.2281 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	DP
actuator	Toggle
amperage rating	30
indoor/outdoor	Indoor
Load Rating	30 A @ 120/277 VAC
Load Type	CFL, Xenon, Halogen, Incandescent, LED, Fluorescent, Universal
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Descriptions

Description	30A 120/277VAC B+S WIRE DP SW BN
extra long description	P&S PS30AC2 30A 120/277VAC B+S WIRE
Features	Chemical Resistant
Long Description	2-Pole Toggle Switch, Back and Side-Wire, 30A 120/277V
Product Type	30A 120/277VAC B+S Wire DP SW BN
Special Features	Heavy duty switch, back & side wire, with lock

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195545
Manufacturers Part Number	PS30AC2
UPC	785007195545



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2281

Uses, Certifications, and Standards

Application	Commercial/Residential
standard	CULUS, UL20, FEDSPEC