



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS40FBBK 400A 600V Cam Type PLG Series 16 BK

*Pass & Seymour/Legrand*

|                  |                                                               |
|------------------|---------------------------------------------------------------|
| Catalog Number   | PS40FBBK                                                      |
| Manufacturer     | Pass & Seymour/Legrand                                        |
| Description      | 400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow |
| Weight per unit  | 0.7190 (lbs/each)                                             |
| Product Category | Plugs, Connectors, Inlets, Out                                |

### Features

|                 |                                                                      |
|-----------------|----------------------------------------------------------------------|
| amperage rating | 400                                                                  |
| Cord Type       | Individual conductor, Type SC, SCE, SCT or W, 75°C, copper wire only |
| indoor/outdoor  | Indoor                                                               |
| Poles           | 1                                                                    |
| Voltage         | 600.0 V                                                              |
| Voltage Rating  | 600                                                                  |
| Wire Size       | 2/0 - 4/0                                                            |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|

### Dimensions and Weight

|      |     |
|------|-----|
| Size | 6.8 |
|------|-----|

### Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 400A 600V CAM TYPE PLG SERIES 16 BK                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| extra long description | P&S PS40FBBK 400A 600V CAM TYPE PLG                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Features               | Chemical Resistant                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Long Description       | 400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Product Type           | 400A 600V Cam Type PLG Series 16 BK                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Special Features       | Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim b |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007308150   |
| Manufacturers Part Number | PS40-FBBK        |
| UPC                       | 785007308150     |

## Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type                 | CONNECTOR                  |

## Trade Size

|          |       |
|----------|-------|
| Amperage | 400.0 |
|----------|-------|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 10    |
| Weight Per each | 0.719 |

## Uses, Certifications, and Standards

|                          |                                                                                                                                    |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Application              | Commercial/Industrial                                                                                                              |
| environmental conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |
| nema rating              | NEMA 3R and 4 for indoor applications                                                                                              |
| Operating Temperature    | -40°-75°C                                                                                                                          |
| standard                 | UL, cCSAus                                                                                                                         |