



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4509 Texoma Parkway
75090-0000, TX Sherman
Phone: 903-892-8041
Fax: 903-892-8907



PS40MCG Cam Prod Male Prot Cap GN

Pass & Seymour/Legrand

Catalog Number	PS40MCG
Manufacturer	Pass & Seymour/Legrand
Description	Cam Prod Male Prot Cap
Weight per unit	0.1050 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	400
Material	Nylon
Voltage	600.0 V
Voltage Rating	600
Wire Size	2 – 4/0

Descriptions

Description	CAM PROD MALE PROT CAP GN
extra long description	P&S PS40MCG CAM PROD MALE PROT CAP
Features	CAM PROD MALE PROT CAP
Long Description	CAM PROD MALE PROT CAP
Product Type	Cam Prod Male Prot Cap Green
Special Features	Built with top-quality materials for example, the chemical- and impact-resistant thermoplastic elastomer bodies on our inline products. That means enhanced durability and service life, with increased insulation protection for safety. And those bodies are available in a variety of colors, for quick and easy phase indication.

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007308440
Manufacturers Part Number	PS40-MCG
UPC	785007308440

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Cam-Type Device Protective Cap

Trade Size

Amperage	400.0
----------	-------

Packaging

Carton	1
Package	50
Weight Per each	0.105



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4509 Texoma Parkway
75090-0000, TX Sherman
Phone: 903-892-8041
Fax: 903-892-8907

Uses, Certifications, and Standards

Application

P&S Cam-Type Devices are a worry-free choice for: Movie and other entertainment production Stage productions Fairs and carnivals Theme parks Concert venues Arenas and convention centers Mining and construction Shipping Airports Many other portable/temporary applications No compat

environmental conditions

UL94 V2, Maximum Continuous +75°C, minimum -40°C without impact

nema rating

NEMA 3R and 4 for indoor applications

standard

UL Listed, CSA Listed