



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2414 Montgomery Ln.
71111-0000, LA Bossier City
Phone: 318-746-5712
Fax: 318-746-8036



PS5266XHG Straight Blade Plug 3W 15A 125V HG

Pass & Seymour/Legrand

Catalog Number	PS5266XHG
Manufacturer	Pass & Seymour/Legrand
Description	Hospital Grade Plug, 15 A, 125 V, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 1.516 In;0.230 to 0.690 In (Cord) Diameter, 2.791 In Length, #18 to #10 Awg Wire Size, Chemical Resistant, Impact Resistant, Corrosion Resistant, 0.164 LB
Weight per unit	0.1632 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Wire Grounding
indoor/outdoor	Indoor
Poles	2
Voltage	125.0 V
Voltage Rating	125

Dimensions and Weight

Size	2.8 in
------	--------

Descriptions

Description	STR BLD PLUG 3W 15A 125V HG
extra long description	P&S PS5266XHG STR BLD PLUG 3W 15A 1

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007236774
Manufacturers Part Number	PS5266XHG
UPC	785007236774

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	PLUG

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.1632

Uses, Certifications, and Standards

standard	FEDSPEC, CULUS, UL 498, FEDSPEC
----------	---------------------------------