



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.
76504-0000, TX Temple
Phone: 254-899-2800
Fax: 254-899-2805



PS5269XHG Straight Blade Conn 3W 15A 125V HG

Pass & Seymour/Legrand

Catalog Number	PS5269XHG
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Connector 2-Pole 3-Wire 15A 125V Hospital Grade
Weight per unit	0.1784 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3.0
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 0 AWG

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	2.64"
------	-------

Descriptions

Description	STR BLD CONN 3W 15A 125V HG
extra long description	P&S PS5269XHG STR BLD CONN 3W 15A 1
Features	Chemical Resistant
Long Description	Straight Blade Connector 2-Pole 3-Wire 15A 125V Hospital Grade
Product Type	STR BLD Conn 3W 15A 125V HG
Special Features	Ready to wire, nylon housing, rugged 2pc cord grip

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007237290
Manufacturers Part Number	PS5269-XHG
UPC	785007237290

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Straight Blade, Connector

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.
76504-0000, TX Temple
Phone: 254-899-2800
Fax: 254-899-2805

Packaging

Carton	1
Package	50
Weight Per each	0.1784

Uses, Certifications, and Standards

Application	Industrial
nema rating	5-15R
standard	FEDSPEC, CULUS, UL498, FEDSPEC