



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger
88240-0000, NM Hobbs
Phone: 575-397-2122
Fax: 575-397-2178



PS5669X Straight Blade Conn 3W 15A 250V B&W

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PS5669X |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Connector 2-Pole 3-Wire 15A 250V |
| Weight per unit | 0.1700 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|------------|
| amperage rating | 15 |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Number of Wires | 3.0 |
| Poles | 2 |
| Voltage | 250.0 V |
| Voltage Rating | 250 |
| Wire Size | 14 - 0 AWG |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|-------|
| Size | 2.64" |
|------|-------|

Descriptions

| | |
|------------------------|--|
| Description | STR BLD CONN 3W 15A 250V B&W |
| extra long description | P&S PS5669X STR BLD CONN 3W 15A 250 |
| Features | Chemical Resistant |
| Long Description | Straight Blade Connector 2-Pole 3-Wire 15A 250V |
| Product Type | STR BLD Conn 3W 15A 250V B&W |
| Special Features | Ready to wire, nylon housing, rugged 2pc cord grip |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007237177 |
| Manufacturers Part Number | PS5669-X |
| UPC | 785007237177 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | CONNECTOR |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger
88240-0000, NM Hobbs
Phone: 575-397-2122
Fax: 575-397-2178

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.17 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------------------|
| Application | Industrial |
| nema rating | 6-15R |
| standard | FEDSPEC, CULUS, UL498, FEDSPEC |