



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



PS5965Y Straight Blade Maxgrip Plug 3W 15A 125V YI

Pass & Seymour/Legrand

Catalog Number	PS5965Y
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Max Grip Plug, 15 A, 125 V, 2 Poles, 3 Wires, Yellow, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 0.22 to 0.66 In (Cord) Diameter, 1.83 In Length, #18 to #12 Awg Wire Size, Crush/Impact Resistant, Arc Resistant, 0.15 LB
Weight per unit	0.1476 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Wire Grounding
indoor/outdoor	Indoor
Poles	2
Voltage	125.0 V
Voltage Rating	125

Dimensions and Weight

Size	1.83 in
------	---------

Descriptions

Description	STR BLD MAXGRIP PLUG 3W 15A 125V Y
extra long description	P&S PS5965Y STR BLD MAXGRIP PLUG 3W

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007237467
Manufacturers Part Number	PS5965Y
UPC	785007237467

Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	Straight Blade

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.1476

Uses, Certifications, and Standards

standard	CULUS, UL 498
----------	---------------