



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PSL715P 15A 3W 277V TL Plug

Pass & Seymour/Legrand

Catalog Number	PSL715P
Manufacturer	Pass & Seymour/Legrand
Description	
Weight per unit	0.1600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15 A
Material	NYLON
Number of Wires	3 in
Poles	2 in
Voltage Rating	277 VAC
Wire Size	4 in

Material, Color, and Finish

Color	BLACK/WHITE
-------	-------------

Dimensions and Weight

Size	3.8 in
------	--------

Descriptions

Description	15A 3W 277V TL PLUG
Product Type	Turnlok Plug 3W 15A 277V
Special Features	Locking Device, impact resistant

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007236613
Manufacturers Part Number	PSL715-P
sub brand	Pass & Seymour
UPC	785007236613

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlock Plug

Packaging

Carton	10
Package	50
Weight Per each	0.16



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Industrial Spec Grade
Mounting	Plug
nema rating	L7-15P
standard	UL 498

15 AMP NEMA L715 PLUG - BLACK BACK, WHITE FRONT BODY

PSL715P | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Plug 3wire 15amp 277v



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

SPECIFICATIONS

GENERAL INFO

Color: Black, White

Type: Plug

Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: 498

UL Standard: Yes
UN SPSC: 39121403
UR: No

DIMENSIONS

Diameter (US): 1.516"
Length (US): 2.617"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: L715
Volts: 277V
Volts (AC): 277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

