

Specifications

Eaton PT18M-C2

Eaton Accell minute timer, 5, 10, 15, 30, and 60 minute default settings, 15A, 120V, Wire leads, Five button, Light almond, white, ivory, Load type: Incandescent, halogen, MLV, ELV, fluorescent, CFL, LED, Single-pole, Polycarbonate, 1800W

General specifications

PRODUCT NAME	Eaton Accell minute timer
CATALOG NUMBER	PT18M-C2
UPC	032664723407
PRODUCT LENGTH/DEPTH	1.8 in
PRODUCT HEIGHT	3.81 in
PRODUCT WIDTH	1.39 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	cULus Listed
CERTIFICATIONS	NOM
PRODUCT TYPE	Accell minute timer



Powering Business Worldwide

Product specifications

WATTAGE	1800 W
SPECIAL FEATURES	5, 10, 15, 30, and 60 minute default time settings
TYPE	Accell minute timer
AMPERAGE RATING	15A
VOLTAGE RATING	120 V
CONFIGURATION	Five button
WIRING METHOD	Wire leads
SWITCH TYPE	Single-pole
LOAD TYPE	LED MLV HAL INC FLR CFL ELV
MATERIAL	Polycarbonate
COLOR	White Ivory Light almond

Resources

MULTIMEDIA	How to change the faceplate color on your Eaton timer
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PT18M-C2 5-Button timers spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

