## PT8300RED

# **legrand**<sup>®</sup> designed to be better.

# PlugTail<sup>™</sup> Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Red

PT8300RED



PlugTail<sup>™</sup> Extra Heavy-Duty Hospital Grade Duplex Receptacle 20amp 125volt Red



# features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

specifications

#### **General Info**

Color: red Product Series: PlugTail Type: Receptacles Duty: Extra Heavy Duty

### Listing Agencies/Third Party Information

cULus: Yes Federal Spec: Yes Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406 UR: No

#### Dimensions

Depth U S: .866" Height U S: 3.281" Width U S: 1.625"

### **Technical Information**

Amps: 20 Amp Volts: 125V Volts A C: 125 Capacity: Duplex Grade Type: Hospital

# **Buy American Act Compliance**

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant