



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1014RD 10-12AWG 1/4"STD Ylw Insltd Ring TRML *Panduit Corporation*

Catalog Number	PV1014RD
Manufacturer	Panduit Corporation
Description	The PV10-14R-D Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0057 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	1/4"
------	------

Descriptions

Description	10-12AWG 1/4"STD YLW INSLTD RING TRML
extra long description	PAN PV10-14R-D Pan-Term® PV10-14R-D
Long Description	The PV10-14R-D Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV10-14R-D Ring Terminal, Yellow, Vinyl, 10-12 Awg

Manufacturer Information

Brand	Panduit®
GTIN	00074983801350
Manufacturers Part Number	PV10-14R-D
UPC	074983801350

Taxonomies, Classifications, and Categories

Type	Ring Terminal
------	---------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 500

Packaging

Carton 500

Weight Per each 0.0057

Uses, Certifications, and Standards

Enclosure Ring shape

Mounting 5/16

standard cULus Listed 587H E52164, CSA Certified LR31212

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)