ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

PV1410LFNC 18-14 Vnyl Ins LCKNG FRK TRM Blu # 10 Stud NRW TNG

Panduit Corporation

Catalog Number	PV1410LFNC
Manufacturer	Panduit Corporation
Description	Locking Fork Terminal, Vinyl Insulated, Funnel Entry, 18- 14 Awg, #10 Stud Size, Narrow Tongue, Standard Package.
Weight per unit	0.2900 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#10

Descriptions

Description	18-14 VNYL INS LCKNG FRK TRM BLU # 10 STUD NRW TNG
extra long description	PAN PV14-10LFN-C Pan-Term® PV14-10L
Long Description	Locking Fork Terminal, vinyl insulated, funnel entry, 18- 14 AWG, #10 stud size, narrow tongue, standard package.
Product Type	Pan-Term® PV14-10LFN-C Loose Piece Terminal

Manufacturer Information

Brand	PANDUIT
GTIN	00074983808700
Manufacturers Part Number	PV14-10LFN-C
UPC	074983808700

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal

Availability

minimum qty	100

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Package	500
Weight Per each	0.29

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	5/16
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)