

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



Outer Diameter

PV2010CT00 Plasta Bond 2INCH Ridged Pipe *Calpipe Industries, Inc*

Manufacturer Calpipe Industries, Inc Rigid Conduit, Steel Material; Hot Dip Galvanized, 0.002 Urethane Coated Interior, 0.04 Inch PVC Coated Exterior 10 Foot; 2.083 Inch Inner Diameter; 2.455 Inch Outer D UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable S Weight per unit N/A	! Inch			
Urethane Coated Interior, 0.04 Inch PVC Coated Exterior 10 Foot; 2.083 Inch Inner Diameter; 2.455 Inch Outer D UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable S	? Inch			
Weight per unit N/A	r Finish; iameter;			
Product Category 20250313130519	20250313130519			
Features				
Applicable Standard ANSI C80.1, NEMA RN-1				
End Style Threaded				
Material Steel				
Wall Thickness 0.146 INCH	0.146 INCH			
Material, Color, and Finish				
Finish Hot Dip Galvanized, 0.002 Inch Urethane Coated Interior	or, 0.04			
Dimensions and Weight				
Inner Diameter 2.083 INCH				
Length 10 Foot				

2.455 INCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

_			•			
De	~~	~r	ın		$\boldsymbol{\sim}$	n
\mathbf{r}	~~	•		•	v	
			•			

Approval

Descriptions	
Additional Information	Constructional Feature Corrosion Resistant; Includes Coupling; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mil
Commodity Description	Pvc Schedule 40 Conduit
extra long description	STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 2.083 INCH INNER DIAMETER; 2.455 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 376 POUND PER 100 FOOT WEIGHT; 300 FOOT PER BUNDLE STANDARD PACKAGE; 2 INCH TRADE SIZE; 0.146 INCH WALL THICKNESS; THREADED END STYLE; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; INCLUDES COUPLING; PV MODEL
Long Description	RIGID CONDUIT, STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 10 FOOT; 2.083 INCH INNER DIAMETER; 2.455 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD
Product Type	Rigid Conduit
Manufacturer Information	
Brand	CALBOND
GTIN	00847656076375
Manufacturers Part Number	PV2010CT00
Model	PV
UPC	847656076375
Taxonomies, Classifications, and Cate	gories
Category Description	Fuses & Fuse Accessories
Trade Size	
Trade Size	2 INCH
Packaging	
Carton	1
Standard Package	300 Foot per Bundle
Weight	274 Dound nor 100 Foot
Weight Per each	0
Uses, Certifications, and Standards	

UL 6, CUL