



Part Number	Size	T Min.	OD	ID Min.	E	B	D Min.	L Min.
A52AE12	½"	0.109"	0.840"	0.578"	0.852"	0.836"	1.500"	120"
A52AG12	¾"	0.113"	1.050"	0.780"	1.064"	1.046"	1.750"	120"
A52BA12	1"	0.133"	1.315"	1.004"	1.330"	1.310"	2.000"	120"
A52BC12	1 ¼"	0.140"	1.660"	1.335"	1.677"	1.655"	2.250"	120"
A52BE12	1 ½"	0.145"	1.900"	1.564"	1.918"	1.894"	2.500"	120"
A52CA12	2"	0.154"	2.375"	2.021"	2.393"	2.369"	3.000"	120"
A52CE12	2 ½"	0.203"	2.875"	2.414"	2.890"	2.868"	3.250"	120"
A52DA12	3"	0.216"	3.500"	3.008"	3.515"	3.492"	3.750"	120"
A52DE12	3 ½"	0.226"	4.000"	3.486"	4.015"	3.992"	4.000"	120"
A52EA12	4"	0.237"	4.500"	3.961"	4.515"	4.491"	4.500"	120"
A52FA12	5"	0.258"	5.563"	4.975"	5.593"	5.553"	5.500"	120"
A52GA12	6"	0.280"	6.625"	5.986"	6.658"	6.614"	6.125"	120"
A52JA12	8"	0.322"	8.625"	7.853"	8.670"	8.610"	6.375"	120"

Dimensions are Nominal

ETL Listed  
 Conforms to UL651  
 NEMA TC2 Compliant  
 See NEC Article 352 for use  
 Sunlight Resistant  
 Max 90° C Wire



**CANTEX**  
 INC.  
 Fort Worth, TEXAS

**Schedule 40 10' Rigid PVC Conduit**

Drawn By: O.M.

Date: 4/26/26

Ref. A52AE12